

POWDER INDUCTION PRODUCTS

Four ways to induce powder in-line



Specification	SHEAR-blend	POWDER-max	DRY-blend	SIMPLE-blend
Ideal operating flow rate (low viscosity)	50 – 510 GPM 11 – 116 m ³ /hr	30 – 210 GPM 7 – 48 m ³ /hr	40 – 150 GPM 9 – 34 m ³ /hr	30 – 210 GPM 7 – 48 m ³ /hr
Powder feed rates (highly soluble)	Up to 150#/min 68 kg/min	Up to 300#/min 136 kg/min	Up to 350#/min 159 kg/min	Up to 300#/min 147 kg/min
Maximum viscosity	1000 cPs	2500 cPs*	2500 cPs*	2500 cPs*
Dynamic shearing teeth	Yes	Yes	No	No

* May require a supply or take-away pump